

Marvel™ Maxx Pearl versus Marvel™ Maxx 2

DOPLAR™ TEST



Marvel™ Maxx Pearl
 NRG™ Smooth Pearl Reactive
 1500-grit Polished
 Centripetal™ Core

→ **Marvel™ Maxx Pearl**
 Laydown: 21.95
 Launch Angle: -2.30°
 Break Point: 43.00'
 Impact Point: 17.48




Marvel™ Maxx 2
 NRG™ Smooth Solid Reactive
 1500-grit Polished
 Centripetal™ Core


→ **Marvel™ Maxx 2**
 Laydown: 26.92
 Launch Angle: -3.00°
 Break Point: 42.93'
 Impact Point: 17.87

Marvel Maxx Pearl versus Marvel Maxx 2

- The Marvel Maxx Pearl pushed ~5' further.
- The Marvel Maxx Pearl setdown was 5 boards further right.
- Both balls finished well in the pocket.
- The Marvel Maxx 2 generated 10% more midlane read.



Pattern: KK-Middle Road



Tester: Steve Kloempken
 Delivery: Right Hand Tweener
 Rev Rate: 345 RPM
 Rotation: 65°
 Tilt: 13°

